

Wall Mounted Water Distillation Unit

Item Number: KT-C01



Introduction

The wall mounted water distillation unit can be installed on the wall and is designed to produce high-quality distilled water continuously, automatically and efficiently at low economic cost.

[Learn More](#)

Model	KT-3.5~4.5L/h
Power supply	AC220V~240V/50Hz -60Hz
Water output	3.5-4.5L/h
Power	1.5Kw x2
Net weight	7kg/set
Gross weight	8kg/set
Box size	740x400x140mm/set
Evaporator volume	5.5liter
PH value	5-6