

Waste Plastic Pyrolysis Plant

Item Number: WPRE



Introduction

This device is heated by a horizontal rotary heating furnace, which can be used for continuous production and processing capacity; 20-30 tons/day can process tire oil to produce diesel and by-products.

[Learn More](#)

Model	Daily throughput	Continuous
LL-10	10 tons/day	Continuous
LL-20	20 tons/day	Continuous
LL-30	30 tons/day	Continuous
LL-50	50 tons/day	Continuous
LL-100	100 tons/day	Continuous