

Double Layer Five-Port Water Bath Electrolytic Electrochemical Cell

Item Number: ELCW



Introduction

Experience optimal performance with our Water Bath Electrolytic Cell. Our double-layer, five-port design boasts corrosion resistance and longevity. Customizable to fit your specific needs. View specs now.

[Learn More](#)

Specification	50ml ~ 500ml
Applicable temperature range	0 ~ 60°C
Sealed form	Thread + Apron
Material	Boron glass + PTFE
Electrolytic cell hole	Three electrode holes (6mm), two air holes (3mm), custom openings are available