

H-Type Double-Layer Optical Electrolytic Electrochemical Cell With Water Bath

Item Number: ELCHD



Introduction

Double-layer H-type optical water bath electrolytic cells, with excellent corrosion resistance and a wide range of specifications available. Customization options are also available.

[Learn More](#)

Specification	10ml ~ 1000ml
Applicable temperature range	0 ~ 60°C
Sealed form	Thread + Apron
Material	Boron glass + PTFE
Electrolytic cell hole	Three electrode holes (6mm), two air holes (3mm), custom openings are available