



KINTEK SOLUTION

Cold Isostatic Press Catalog

Contact us for more catalogs of [Sample Preparation](#), [Thermal Equipment](#), [Lab Consumables & Materials](#), [Bio-Chem Equipment](#), etc.

KINTEK SOLUTION

COMPANY PROFILE

>>> About Us

Company Profile

Kintek Solution Ltd is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.

Products & Services

Kintek Solution Ltd is headquartered in Zhengzhou, the capital city of Henan Province, China, and its core business includes the manufacture, distribution and sale of all types of scientific research equipment and laboratory consumables. The wide range of products and services covers the following main areas:

- **Sample Preparation Equipment:** We provide high-performance sample preparation equipment such as tablet presses, ball mills, vibrating sieves and tablet punching machines, which are capable of meeting a wide range of sample preparation needs and ensuring high quality experimental data and research results.
- **Thermal Equipment:** Our thermal equipment includes tube furnaces, sintering furnaces, vacuum furnaces, atmosphere furnaces, graphite furnaces, dental furnaces, rotary furnaces, and high-temperature furnaces (e.g., MPCVD, CVD, PECVD, electric rotary kilns). These facilities excel in high-temperature processing and materials synthesis, meeting a wide range of needs from basic research to industrial production.
- **Biochemical equipment:** We offer a wide range of biochemical laboratory equipment, including rotary evaporators, vacuum pumps, cold trap chillers,

heating circulators, reactors, short-range distillation equipment, sterilization equipment, and homogenizers. These equipments are widely used in the fields of chemical reaction, biological processing and pharmaceutical manufacturing.

- **Laboratory Consumables:** We supply a wide range of laboratory consumables such as fine ceramic products, electrochemical consumables, PTFE material products, high purity materials, battery materials, chemical vapor deposition materials, optical materials, thin film deposition components and glass materials. These consumables provide the necessary support for laboratories to ensure the smooth running of experimental processes.

Technological Advantages

Kintek Solution Ltd has significant technological strengths in the field of scientific research equipment and technical solutions, which enable us to stand out in a competitive marketplace and support our customers with cutting-edge technology. The following are our key technological strengths:

Advanced R&D capabilities

- **Technological Innovation:** Our R&D team is committed to exploring and developing the latest technologies to keep our equipment at the forefront of the industry through continuous technological innovation.
- **Customized solutions:** Based on the specific needs of our customers, we are able to develop and provide customized equipment to meet specific research requirements and application scenarios.
- **Cooperative R&D:** We cooperate with leading research institutes and higher education institutions around the world to carry out R&D projects on cutting-edge technologies to ensure that our technologies are always at the forefront of the industry.

High-performance equipment

- **Precision design:** Our equipment adopts advanced design concepts to ensure high precision, reliability and performance to meet the stringent requirements of scientific research and industrial applications.
- **Advanced materials:** We use high-quality materials and components to improve the durability and stability of our equipment, extend its service life and reduce maintenance costs.

Strict quality control

- Standardized production: All equipment is manufactured in accordance with international quality standards, and each production step is strictly controlled to ensure product consistency and reliability.
- Comprehensive testing: Comprehensive performance testing and quality inspection are carried out before the equipment is delivered to ensure that it meets the customer's technical specifications and operational requirements.

Comprehensive technical support

- Technical Service: Provide comprehensive technical support and after-sales service, including equipment installation, commissioning, training and maintenance, to ensure that customers can use our products efficiently.
- Rapid Response: We have established a rapid response mechanism, which can promptly solve the problems encountered by customers in the process of use and reduce equipment downtime.

Innovative technology integration

- System Integration: We integrate advanced control systems and automation technologies into our equipment to improve operational efficiency and data accuracy, and streamline operational processes.

Through these technological advantages, Kintek Solution Ltd is able to continue to provide our customers with innovative, efficient and reliable scientific research equipment and solutions to promote the continuous progress of scientific research and industrial applications.

Market position and customers

Kintek Solution Ltd is positioned in the market as a leading global provider of high-tech research equipment and solutions, specializing in biochemical reactions, new materials research, heat treatment, vacuum manufacturing, refrigeration, as well as pharmaceuticals and oil extraction. We are committed to brand leadership in research equipment by providing innovative technology and high quality equipment to meet the needs of research organizations and industrial companies in complex research and production processes.

Core Market Positioning:

- **Specialization:** We focus on high technology and scientific research, providing advanced equipment and solutions for specialized research institutes, laboratories and industrial applications.
- **High-end customers:** Our main customers include world-renowned universities, research institutes and various industrial enterprises, which usually have high requirements for equipment performance and technology.
- **Technological Innovation:** We are committed to technological innovation and customized solutions to ensure that our customers receive cutting-edge technical support to meet the ever-changing needs and challenges in the market.

Market Customer Groups:

- **Research Institutes and Universities:** including the world's leading research institutes and institutions of higher learning, who require high-performance research equipment and technical support for basic research, applied research and technology development.
- **Industrial companies:** covering a wide range of industries such as pharmaceuticals, oil extraction, new materials manufacturing and electronic materials production, these companies rely on reliable equipment and solutions to ensure product quality and productivity during production.
- **Laboratories and test centers:** organizations that provide laboratory services and quality testing, requiring accurate laboratory equipment and instruments for sample analysis and testing.
- **Technology Development Companies:** Companies that specialize in the development and application of new technologies and have a high demand for innovative equipment and technical solutions to support their R&D projects and technology validation.

Through clear market positioning and customer groups, we are committed to promoting scientific and technological progress, supporting the innovation and development of our global customers, and continuing to provide high-quality products and services to the market.

Team Introduction

The team at Kintek Solution Ltd is at the heart of the company's success. In order to realize our vision and maintain our leadership position in the field of high-tech research equipment, we are committed to building an exceptional team with the following attributes:

1. Professionalism

- **Technical Expertise:** Our team consists of technical experts and engineers in the field with deep expertise and technical backgrounds to meet complex technical challenges and innovation needs.
- **Industry experience:** We bring together professionals with extensive experience in the fields of research equipment, material science and engineering technology to ensure a precise grasp of market needs and technological trends.

2. Innovative Spirit

- **R&D-driven:** The team encourages innovative thinking and technological exploration, supports employees to participate in R&D projects on cutting-edge technologies, and continuously pushes forward the technological advancement of products and solutions.
- **Flexible Adaptation:** In the face of changing market environment, we have the ability to adapt quickly and flexibly to meet the changing needs of our customers.

3. Collaboration and Communication

- **Cross-sectoral collaboration:** The team maintains close collaboration between various departments, including R&D, production, sales and customer service, to ensure the smooth progress of projects and timely response to customer needs.
- **Efficient Communication:** Emphasize internal communication and information sharing, through efficient communication mechanisms and tools to ensure that all team members are consistent with the project goals and progress.

4. Customer Orientation

- **Customer Service:** Team members are customer-focused and committed to providing quality service and support to ensure that our customers have the best experience in using our products and solutions.

- Customized solutions: the ability to deeply understand the specific needs of customers and provide customized solutions to meet the special requirements of different customers.

5. Professional Training and Development

- Continuous Learning: We provide continuous training and learning opportunities for our team members to ensure that they are always up-to-date with the latest technology and industry knowledge.
- Career Development: We value the career development and growth of our employees, provide clear career paths and promotion opportunities, and motivate our employees to realize their personal goals and career aspirations within the company.

6. Corporate Culture

- Integrity and Responsibility: The team upholds integrity and responsibility, treats work and customers with honesty and fairness, and builds trust and long-term cooperative relationships.
- Unity and Collaboration: Focusing on the spirit of teamwork, the team emphasizes mutual support and joint efforts to achieve the company's goals and promote the overall success of the team.

By building such a highly qualified, innovation-driven and customer-oriented team, we ensure that Kintek Solution Ltd continues to lead in the field of scientific research equipment and provide excellent products and services to our customers worldwide.

At KINTEK, technology fuels our corporate spirit. This dynamic energy awaits you upon joining our team. Expect a distinctive cultural environment where our global business focus opens doors to diverse customs and traditions worldwide. Here, challenging roles promise to propel your career to new heights.

Our exceptional corporate culture sparks innovation, fosters care, and drives continuous progress among individuals and teams. Our team embodies youthfulness, positivity, enthusiasm, and a bold attitude toward challenges. Passionate about our business, our employees ardently contribute to the company's growth.

We seek individuals brave enough to embrace challenges, harbor grand ambitions, and thirst for knowledge. If you're driven by dreams and passion, and aspire to start your

entrepreneurial journey, KINTEK is the platform to actualize your career plans. We don't just offer opportunities; we pave the way for your future.

Join us at KINTEK, where innovation meets opportunity. Let's create a future that's as promising as your aspirations.

Future Plans

Kintek Solution Ltd's future plans are aimed at further strengthening our leadership position in the research equipment sector and driving the company forward in terms of technological innovation, market expansion and customer service. The following are our key future directions:

1. Technology Innovation and R&D

- Cutting-edge technology development: Continue to invest resources in the research and development of cutting-edge technologies, such as artificial intelligence, the Internet of Things and nanotechnology, in order to promote equipment intelligence and automation.
- New Product Lines: Expand existing product lines and develop equipment to meet emerging market needs, especially in the areas of biochemistry, biomedicine and high-performance materials.
- Cooperative R&D: Strengthen cooperation with international research institutes and institutions of higher learning to carry out joint R&D projects to ensure that the technology remains at the global leading level.

2. Market Expansion

- Global Market Expansion: Further expand the global market, especially in emerging markets and developing regions, establish more sales and service networks, and enhance the brand's international influence.
- Industry application: Explore and expand the application fields in other industries, such as new energy, environmental protection technology and intelligent manufacturing, to open up new business growth points.

3. Customer Service Enhancement

- Enhancement of customer support: Establish a more complete customer support system, provide 24/7 technical support and maintenance services, and ensure

the efficient experience of customers in the use of equipment.

- Customized services: Provide more customized services and solutions according to customers' individual needs to enhance customer satisfaction and loyalty.

4. Sustainable Development

- Environmentally friendly technology: Develop and adopt environmentally friendly materials and processes to reduce the environmental impact during the production and use of equipment and promote sustainable development.
- Energy saving and consumption reduction: Optimize the energy efficiency of equipment, reduce energy consumption, improve resource utilization efficiency, and support the development of green technology.

5. Internal optimization

- Intelligent management: Implement intelligent management systems and data analysis tools to improve productivity and management and reduce operating costs.
- Employee Training: Enhance employee training and skills upgrading to build a high-quality team to meet changing market demands and technological challenges.

6. Innovation ecosystem

- Establishment of innovation platform: Create innovation platforms and laboratories to support employees and partners in technological innovation and product development.
- Industry Chain Cooperation: Deepen cooperation with the upstream and downstream of the industry chain, integrate resources, and promote the development and implementation of industry technical standards and market norms.

Through these future plans, Kintek Solution Ltd will continue to lead the forefront of science and technology, provide customers with more advanced and reliable products and services, and at the same time, promote the sustainable development of the enterprise and the progress of the industry.



Electric Lab Cold Isostatic Press (Cip) 12T / 20T / 40T / 60T

Item Number: PCIE



Introduction

Produce dense, uniform parts with improved mechanical properties with our Electric Lab Cold Isostatic Press. Widely used in material research, pharmacy, and electronic industries. Efficient, compact, and vacuum-compatible.

[Learn More](#)

Instrument model	PCIE-12T	PCIE-20T	PCIE-40T	PCIE-60T
Pressure Range	0-12T(0-17MPa)	0-20T(0-21MPa)	0-40T(0-30MPa)	0-60T(0-34MPa)
Piston diameter	95mm (d) in chrome plated oil cylinder	110mm (d) in chrome plated oil cylinder	130mm (d) in chrome plated oil cylinder	150mm (d) in chrome plated oil cylinder
Pressure gage	Digital display0.0-40.0MPa	Digital display0.0-40.0MPa	Digital display0.0-40.0MPa	Digital display0.0-40.0MPa
Maximum piston stroke (T)	40mm	40mm	50mm	50mm
Way of Pressure	Electric pressurization/manual pressurization	Electric pressurization/manual pressurization	Electric pressurization/manual pressurization	Electric pressurization/manual pressurization
Pressure replenishment method	Automatic pressurization/manual slow pressurization	Automatic pressurization/manual slow pressurization	Automatic pressurization/manual slow pressurization	Automatic pressurization/manual slow pressurization
guard	Organic glass	Organic glass	Organic glass	Organic glass
ambient temperature	10°C-40°C	10°C-40°C	10°C-40°C	10°C-40°C
Isostatic pressure	0-300MPa	0-300MPa	0-300MPa	0-300MPa
Isostatic pressure chamber	Φ22×70mm(M×N)	Φ30×120mm(M×N)	Φ40×150mm(M×N)	Φ50×150mm(M×N)
External dimensions	305×430×530mm(L×W×H)	305×430×600mm(L×W×H)	355×450×710mm(L×W×H)	405×470×720mm(L×W×H)
power supply	550W(220V/110 can be customized)	550W(220V/110 can be customized)	550W(220V/110 can be customized)	550W(220V/110 can be customized)
Equipment weight	110Kg	120Kg	150Kg	200Kg

Manual Cold Isostatic Pellet Press (Cip) 12T / 20T / 40T / 60T

Item Number: PCIM



Introduction

Lab Manual Isostatic Press is a high-efficient equipment for sample preparation widely used in material research, pharmacy, ceramics, and electronic industries. It allows for precision control of the pressing process and can work in a vacuum environment.

[Learn More](#)

Instrument model	PCIM-12T	PCIM-20T	PCIM-40T	PCIM-60T
Pressure Range	0-12T(0-17MPa)	0-20T(0-21MPa)	0-40T(0-30MPa)	0-60T(0-34MPa)
Piston diameter	95mm (d) in chrome plated oil cylinder	110mm (d) in chrome plated oil cylinder	130mm (d) in chrome plated oil cylinder	150mm (d) in chrome plated oil cylinder
Pressure gage	Pressure and pressure dual scale display	Pressure and pressure dual scale display	Pressure and pressure dual scale display	Pressure and pressure dual scale display
Maximum piston stroke (T)	40mm	40mm	50mm	50mm
Guard	Organic glass	Organic glass	Organic glass	Organic glass
Ambient temperature	10°C-40°C	10°C-40°C	10°C-40°C	10°C-40°C
Isostatic pressure	0-300MPa	0-300MPa	0-300MPa	0-300MPa
Isostatic pressure chamber	Φ22×70mm(M×N)	Φ30×120mm(M×N)	Φ40×150mm(M×N)	Φ50×150mm(M×N)
External dimensions	305×195×530mm(L×W×H)	305×195×600mm(L×W×H)	355×215×710mm(L×W×H)	405×240×720mm(L×W×H)
Equipment weight	90Kg	100Kg	130Kg	180Kg

Pressure conversion		
Actual pressure	Chamber pressure	System pressure
1.7 [Tons]	1.86 [MPa]	25 [MPa]
3.5 [Tons]	3.72 [MPa]	50 [MPa]
5 [Tons]	5.57 [MPa]	75 [MPa]
7 [Tons]	7.43 [MPa]	100 [MPa]
8.7 [Tons]	9.29 [MPa]	125 [MPa]
10.5 [Tons]	11.2 [MPa]	150 [MPa]
14 [Tons]	14.8 [MPa]	200 [MPa]
17.5 [Tons]	18.6 [MPa]	250 [MPa]
21 [Tons]	22.3 [MPa]	300 [MPa]

Reminder: Generally, the system pressure should not exceed 35MPa, otherwise it will affect the service life of the equipment.

Electric Split Lab Cold Isostatic Press (Cip) 65T / 100T / 150T / 200T

Item Number: PCESI



Introduction

Split cold isostatic presses are capable of providing higher pressures, making them suitable for testing applications that require high pressure levels.

[Learn More](#)

Instrument model	PCESI-65T	PCESI-100T	PCESI-150T	PCESI-200T
Pressure Range	0-65T	0-100T	0-150T	0-200T
Piston diameter	160mm (d) in chrome plated oil cylinder	200mm (d) in chrome plated oil cylinder	200mm (d) in chrome plated oil cylinder	290mm (d) in chrome plated oil cylinder
Pressurization process	Program pressurization - Program holding -Timed pressure relief	Program pressurization -Program holding -Timed pressure relief	Program pressurization - Program holding-Timed pressure relief	Program pressurization - Program holding -Timed pressure relief
Pressure conversion	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample
Display	7-inch LCD screen	7-inch LCD screen	7-inch LCD screen	7-inch LCD screen
Equipment protection	Steel plate protection with organicglass door	Steel plate protection with organicglass door	Steel plate protection with organic glass door	Steel plate protection with organicglass door
Isostatic pressure	0-300MPa	0-300MPa	0-300MPa	0-300MPa
Isostatic pressure chamber	Φ50×150mm(M×N)	Φ60×150mm(M×N)	Φ80×150mm(M×N)	Φ90×150mm(M×N)
Cylinder stroke (T)	50mm	50mm	50mm	50mm
Space size	220×400mm(M×N)	260×400mm(M×N)	280×400mm(M×N)	290×420mm(M×N)
External dimensions	700×450×1050mm(L×W×H)	850×500×1100mm(L×W×H)	950×550×1150mm(L×W×H)	1000×650×1200mm(L×W×H)
Equipment power supply	1500W(220V/110 can be customized)	1500W (220V/110 can be customized)	1500W(220V/110 can be customized)	1500W(220V/110 can be customized)
Equipment weight	350kg	580kg	680kg	980kg

Automatic Lab Cold Isostatic Press (Cip) 300Mpa-400Mpa-500Mpa

Item Number: PCIA



Introduction

Efficiently prepare samples with our Automatic Lab Cold Isostatic Press. Widely used in material research, pharmacy, and electronic industries. Provides greater flexibility and control compared to electric CIPs.

[Learn More](#)

Instrument model	PCIA-20T	PCIA-40T	PCIA-60T	PCIA-100T
Piston diameter	110mm (d) in chrome plated oil cylinder	130mm (d) in chrome plated oil cylinder	150mm (d) in chrome plated oil cylinder	200mm (d) in chrome plated oil cylinder
Pressurization process	Program pressurization - Program holding -Timed pressure relief	Program pressurization - Program holding -Timed pressure relief	Program pressurization - Program holding -Timed pressure relief	Program pressurization - Program holding -Timed pressure relief
Pressure conversion	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample	The program automatically converts the pressure borne by the sample
Display	4.3 inch LCD screen	4.3 inch LCD screen	4.3 inch LCD screen	7 inch LCD screen
Equipment protection	Steel plate protection with organic glass door	Steel plate protection with organic glass door	Steel plate protection with organic glass door	Steel plate protection with organic glass door
Isostatic pressure	300-500MPA	300-500MPA	300-500MPA	300-500MPA
Isostatic pressure chamber	Φ30×150mm(M×N)	Φ40×150mm(M×N)	Φ50×150mm/30×150mm	Φ60×150(M×N)
Cylinder stroke (T)	50mm	50mm	50mm	50mm
Sample making characteristics	Upperpanel rocker arm structure formore convenient operation	Upperpanel rocker arm structure formore convenient operation	Upperpanel rocker arm structure formore convenient operation	Upperpanel rocker arm structure formore convenient operation
External dimensions	240×390×560(L×W×H)	280×460×660(L×W×H)	/	330×580×720(L×W×H)
Equipment power supply	550W(220V/110 can be customized)	550W(220V/110 can be customized)	550W(220V/110 can be customized)	550W(220V/110 can be customized)
Equipmentweight	120KG	180KG	240KG	290KG

Cold Isostatic Press For Small Workpiece Production 400Mpa

Item Number: PCIS



Introduction

Produce uniformly high-density materials with our Cold Isostatic Press. Ideal for compacting small workpieces in production settings. Widely used in powder metallurgy, ceramics, and biopharmaceutical fields for high-pressure sterilization and protein activation.

[Learn More](#)

Model	PCIS-150	PCIS-200	PCIS-250	PCIS-300
Effective inner diameter of high pressure chamber (mm)	150	200	250	300
Effective depth of high pressure cavity (mm)	300	300	300	400/450
Maximum working pressure (MPa)	100-400	100-400	100-400	100-300
Power	9Kw	9Kw	17.5Kw	17.5Kw
Feeding method	Automatic			
Boost rate	Manually adjustable or precisely adjustable			
Working medium	Oil or water+rust inhibitor			
HMI	Text screen or touch screen			
Data export interface	USB			
Cooling method	Water cooling			

Warm Isostatic Press (Wip) Workstation 300Mpa

Item Number: PCIW



Introduction

Discover Warm Isostatic Pressing (WIP) - A cutting-edge technology that enables uniform pressure to shape and press powdered products at a precise temperature. Ideal for complex parts and components in manufacturing.

[Learn More](#)

Model	Cylinder inner diameter (mm)	Cylinder inner height (mm)	Maximum pressure (MPa)	Maximum temperature
PCIW150	Ø150	300-500	300	(Deionized water) ≤ 90°C (heat transfer oil) ≤ 250°C
PCIW200	Ø200	500-1000		
PCIW250	Ø250			
PCIW300	Ø300			
PCIW350	Ø350	500-1500		
PCIW400	Ø400	500-2000		
PCIW450	Ø450			
PCIW500	Ø500	1000-3000		
PCIW630	Ø630			
PCIW710	Ø710			
PCIW800	Ø800			
PCIW910	Ø910			
PCIW1000	Ø1000			

Isostatic Pressing Molds

Item Number: PIPM



Introduction

Explore high-performance isostatic pressing molds for advanced material processing. Ideal for achieving uniform density and strength in manufacturing.

[Learn More](#)



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

